

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:	0193230016
Status:	Active
Overview:	Metric Ring Terminals
Description:	VersaKrimp Metric Ring Terminal for M10 Stud Size (7/16"), Un-insulated
Documents: 3D Model Drawing (PDF) 3D Model (PDF) RoHS Certificate of Compliance (PDF)	
Agency Certification UL E32244	
General Product Family Series Crimp Quality Equipment Overview Product Name Type UPC Ring and Spade Terminals 19323 Yes Metric Ring Terminals VersaKrimp Ring 887191290003	
Physical Barrel Type Insulation Material - Metal Material - Plating Mating Net Weight Packaging Type Stud Size Wire Size AWG Wire Size mm² Closed - Brazed None Copper Alloy Tin 1.839/g Bag M10 N/A 2.50-6.00	
Solder Process Data Lead-freeProcess Capability N/A	
Material Info Engineering Number C6-340-M10	
Reference - Drawing Numbers Sales Drawing SD-19323-001-001	



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant	China RoHS
REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status Low-Halogen	
For more information, please visit Contact US	
China ROHS ELV RoHS Phthalates	Green Image Not Relevant Not Contained

Search Parts in this Series 19323 Series	
Application Tooling FAQ Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document. Global Description Product # PremiumGrade 640030100 Hand Crimp Tool for Krimptite/Versakrimp Terminals and Splices, 10-22 AWG and 6.0mm² - 0.5mm² Crimp Head for the AT-200 Pneumatic Hand Tool ServiceGrade Hand Crimp Tool - Ratchet 640070100 640160038	

This document was generated on 07/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION