This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0193240006
Status: Active
Overview: Metric Ring Terminals
Description: Avikrimp Metric Ring Terminal for Stud Size 5 (M3), Insulated Barrel



Series image - Reference only

Documents:

3D Model
3D Model (PDF)
Drawing (PDF)
RoHS Certificate of Compliance (PDF)

Agency Certification

UL	E32244

General

Product Family	Ring and Spade Terminals
Series	19324
Crimp Quality Equipment	Yes
Overview	Metric Ring Terminals
Product Name	Avikrimp
Type	Ring
UPC	887191290065

Physical

Barrel Type	Closed - Brazed
Flammability	94V-2
Insulation	Nylon (PA)
Material - Metal	Copper Alloy
Material - Plating Mating	Tin
Net Weight	0.915/g
Packaging Type	Bag
Stud Size	M3
Wire Size AWG	N/A

Solder Process Data

Lead-freeProcess Capability	N/A

Material Info

Engineering Number	BB2,5-823-M3

Reference - Drawing Numbers

Sales Drawing	SD-19324-001-001

EU ELV
Not Relevant

EU RoHS | **China RoHS**
Compliant

REACH SVHC
Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free Status
Low-Halogen

For more information, please visit Contact US

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
19324 Series

Application Tooling | **FAQ**

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Avikrimp and Insulkrimp Terminals and Splices, 10-22 AWG and 6.0-0.5mm² (Rings, Spades, Hooks, Block Spades and Flanged Spades)	640010100
Crimp Head for the AT-200 Pneumatic Hand Tool	640050100

ServiceGrade Hand Crimp Tool for Field Repair only, for production use our PremiumGrade Tool	640160036

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION