

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0193240009

Status:

Active

Overview:

Metric Ring Terminals

Description:

Avikrimp Metric Ring Terminal for Stud Size 5 (M3), Insulated Barrel

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E32244

General

Product Family

Ring and Spade Terminals

Series

19324

Crimp Quality Equipment

Yes

Overview

Metric Ring Terminals

Product Name

Avikrimp

Type

Ring

UPC

887191290096

Physical

Barrel Type

Closed - Brazed

Flammability

94V-2

Insulation

Nylon (PA)

Material - Metal

Copper Alloy

Material - Plating Mating

Tin

Net Weight

1.068/g

Packaging Type

Bag

Stud Size

M5

Wire Size AWG

N/A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

Engineering Number

BB2,5-839-M5

Reference - Drawing Numbers

Sales Drawing

SD-19324-001-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant

REACH SVHC

Not Contained Per -

D(2020)9139-DC (19

Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

19324 Series

Application Tooling | [FAQ](#)

Tooling specifications and manuals are

found by selecting the products below.

Crimp Height Specifications are then

contained in the Application Tooling

Specification document.

Global	
Description	Product #
PremiumGrade	640010100
Hand Crimp Tool	
for Avikrimp and	
Insulkrimp Terminals	
and Splices,	
10-22 AWG and	
6.0-0.5mm² (Rings,	
Spades, Hooks,	
Block Spades and	
Flanged Spades)	
Crimp Head for the	640050100
AT-200 Pneumatic	
Hand Tool	

ServiceGrade Hand 640160036
Crimp Tool for Field
Repair only, for
production use our
PremiumGrade Tool

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION