

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0197054301](#)  
**Status:** **Active**  
**Overview:** [PCB Tabs](#)  
**Description:** PCB Tab Quick Disconnect, Male, for Wire, Box, Tab 6.35 x 0.81mm

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-19902-011-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Product Specification PS-19902-013-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-19902-010-001 (PDF)</a>	

**Agency Certification**

UL E79133

**General**

Product Family	Quick Disconnects
Series	<a href="#">19705</a>
Crimp Quality Equipment	Yes
Insulated	No
Overview	<a href="#">PCB Tabs</a>
Product Name	PCB Tab
Type	Quick Disconnect
UPC	800755104783

**Physical**

Barrel Type	N/A
Gender	Male
Glow-Wire Capable	No
Insulation	None
Lock to Mating Part	None
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.490/g
Orientation	PCB Straight Tab
Packaging Type	Bag
Plating min - Mating	3.810µm
Plating min - Termination	2.540µm
Polarized to Mating Part	No
Tab Thickness	0.81mm
Tab Width	6.35mm
Wire Insulation Diameter	N/A
Wire Size AWG	N/A

**Electrical**

Voltage - Maximum N/A


**Solder Process Data**

Lead-free Process Capability N/A

**Material Info**

**Reference - Drawing Numbers**

Product Specification	PS-19902-010-001, PS-19902-011-001, PS-19902-013-001
Sales Drawing	SD-19705-430-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[19705 Series](#)

This document was generated on 08/17/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**