


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0022013037](#)
Status: **Active**
Overview: [KK Interconnect Solutions](#)
Description: KK 254 Crimp Housing, Friction Ramp with Polarizing Ribs, 3 Circuits, Natural

Documents:

3D Model	Packaging Specification 26950002-PK-000 (PDF)
3D Model (PDF)	Test Summary TS-10-07-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification PS-10-07-001 (PDF)	



Agency Certification

CSA	LR19980
UL	E29179

General

Product Family	Crimp Housings
Series	2695
Application	Signal, Wire-to-Board
Overview	KK Interconnect Solutions
Product Name	KK 254
UPC	800753593831

Physical

Circuits (maximum)	3
Color - Resin	Natural (White)
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Resin	Nylon
Net Weight	0.392/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	See Product Specification

Solder Process Data

Lead-freeProcess Capability	N/A
-----------------------------	-----

Material Info

Engineering Number	2695-03RP
--------------------	-----------

Reference - Drawing Numbers

Packaging Specification	26950002-PK-000
Product Specification	PS-10-07-001
Sales Drawing	26950000-SD-000
Test Summary	TS-10-07-001

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[2695](#) Series

Mates With

KK254 PCB Headers [42375](#) , [42377](#) , [42376](#)
, [4030](#) , [6373](#) , [6410](#) , [171856](#) , [171857](#)

Use With

KK Crimp Terminals [2759](#) , [6459](#) , [41572](#)
, [4809](#) , [8088](#)
 KK 254 Pre-Crimped
Leads [797580007](#) , [797580015](#)