

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0022552043](#)  
**Status:** **Active**  
**Overview:** [SL Modular Connectors](#)  
**Description:** 2.54mm Pitch SL Crimp Housing, Dual Row, Version C, Back Ribs, 4 Circuits, Black

**Documents:**

<a href="#">3D Model</a>	<a href="#">Product Specification PS-70400-001 (PDF)</a>
<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary TS-70058-001-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	Crimp Housings
Series	<a href="#">70450</a>
Application	Signal, Wire-to-Board
Comments	Version C
Overview	<a href="#">SL Modular Connectors</a>
Product Name	SL
UPC	800754395786

**Physical**

Breakaway	No
Circuits (maximum)	4
Color - Resin	Black
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Material - Resin	Polyester
Net Weight	0.372/g
Number of Rows	2
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Stackable	Yes
Temperature Range - Operating	-40° to +105°C

**Solder Process Data**


Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

Engineering Number	704500100
--------------------	-----------

**Reference - Drawing Numbers**

Product Specification	PS-70400-001
Sales Drawing	SD-70450-0100-0125-0
Test Summary	TS-70058-001-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[70450 Series](#)

**Mates With**

2.54mm Pitch C-Grid Header [70229](#) , [70280](#)  
, [70246](#) , [70247](#)

**Use With**

[70058](#) , [71851](#)