

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0310671010

Status:

Active

Overview:

H-DAC 64 Unsealed Connector System

Description:

2.54mm H-DAC 64, 3 Way Receptacle Assembly, Single Row, Polarization A

Documents:	
3D Model	Application Specification AS-31067-100-001 (PDF)
Drawing (PDF)	Packaging Specification PK-30907-737-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31301-076-001 (PDF)
Product Specification PS-31100-0001-001 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	31067
Application	Automotive, Power, Wire-to-Board, Wire-to-Wire
Comments	Polarization Option A, Black
Overview	H-DAC 64 Unsealed Connector System
Product Name	H-DAC 64
UPC	800756063041

Physical	
Circuits (maximum)	3
Color - Resin	Black, White
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene, Polyester
Net Weight	1.100/g
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.54mm
Pitch - Termination Interface	2.54mm
Polarized to Mating Part	Yes
Ports	1
Stackable	No
Temperature Range - Operating	-40° to +100°C

Electrical	
Current - Maximum per Contact	11.0A, 9.0A

Solder Process Data	
Lead-freeProcess Capability	N/A

Material Info

Reference - Drawing Numbers	
Application Specification	AS-31067-100-001
Packaging Specification	PK-30907-737-001, PK-31301-076-001
Product Specification	PS-31100-0001-001
Sales Drawing	SD-31109-003-001



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit

Contact US

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series
31067 Series

Mates With
H-DAC 64 3 Way Male Housing Assembly
310671040 , 310671070

Use With
See Product Specification