

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0313721000

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Hybrid Receptacle Assembly, 10 Circuit, Black, Polarization A, without CPA



Series image - Reference only

Documents:	
3D Model	Application Specification AS-31372-100-001 (PDF)
Drawing (PDF)	Application Specification AS-34729-020-001 (PDF)
3D Model (PDF)	Packaging Specification PK-31300-931-001 (PDF)
Product Specification PS-31372-100-001 (PDF)	Brochure (PDF)
Application Specification 347290200-AS-CH-000 (PDF)	RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Housings
Series	31372
Application	Automotive, Power, Wire-to-Board
Comments	Polarization A, 6 x 1.50 and 4 x 2.8
Overview	Stac64 Single, Multi-Pocket and Hybrid Header System
Product Name	Stac64
UPC	822348054497
Physical	
Circuits (maximum)	10
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Modified Polystyrene
Net Weight	8.060/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm, 5.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +100°C
Electrical	
Current - Maximum per Contact	22.0A, 30.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Application Specification	347290200-AS-CH-000, AS-31372-100-001, AS-34729-020-001
Packaging Specification	PK-31300-931-001
Product Specification	PS-31372-100-001
Sales Drawing	313729000-000

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image
Compliant

Not Contained

Search Parts in this Series
31372 Series

Mates With
Stac64 Right Angle Assembly [34696](#) .
Stac64 Vertical Assembly [34695](#)

Use With
MX150 Terminal [33012](#)