

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0349690142

Status:

Active

Overview:

Stac64 Single, Multi-Pocket and Hybrid Header System

Description:

Stac64 Hybrid Receptacle Assembly, 14 Circuit, Brown, Polarization C

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-34969-100-001 (PDF)

Application Specification 347290200-AS-CH-000 (PDF)

Application Specification AS-34729-020-001 (PDF)

Packaging Specification PK-31301-201-001 (PDF)

Brochure (PDF)

RoHS Certificate of Compliance (PDF)

|                               |                                                                                                                                                                     |
|-------------------------------|---------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| General                       |                                                                                                                                                                     |
| Product Family                | Crimp Housings                                                                                                                                                      |
| Series                        | 34969                                                                                                                                                               |
| Application                   | Automotive, Power, Signal, Wire-to-Board                                                                                                                            |
| Comments                      | Current is dependent on connector size, ambient temperature, blade size and related factors. 2.80mm – 30.0A; 0.64mm - 6.0A. . Polarization C, 10 x 0.64 and 4 x 2.8 |
| Overview                      | Stac64 Single, Multi-Pocket and Hybrid Header System                                                                                                                |
| Product Name                  | Stac64                                                                                                                                                              |
| UPC                           | 887191311937                                                                                                                                                        |
| Physical                      |                                                                                                                                                                     |
| Circuits (maximum)            | 14                                                                                                                                                                  |
| Circuits Detail               | 21 x 0.64 and 4 x 2.8                                                                                                                                               |
| Color - Resin                 | Brown                                                                                                                                                               |
| Gender                        | Receptacle                                                                                                                                                          |
| Glow-Wire Capable             | No                                                                                                                                                                  |
| Keying to Mating Part         | Yes                                                                                                                                                                 |
| Lock to Mating Part           | No                                                                                                                                                                  |
| Material - Resin              | Modified Polystyrene                                                                                                                                                |
| Net Weight                    | 8.334/g                                                                                                                                                             |
| Number of Rows                | 2                                                                                                                                                                   |
| Packaging Type                | Carton                                                                                                                                                              |
| Panel Mount                   | No                                                                                                                                                                  |
| Pitch - Mating Interface      | 2.54mm, 5.25mm                                                                                                                                                      |
| Polarized to Mating Part      | Yes                                                                                                                                                                 |
| Ports                         | 1                                                                                                                                                                   |
| Stackable                     | No                                                                                                                                                                  |
| Temperature Range - Operating | -40° to +105°C                                                                                                                                                      |
| Electrical                    |                                                                                                                                                                     |
| Current - Maximum per Contact | 30.0A, 6.0A                                                                                                                                                         |
| Solder Process Data           |                                                                                                                                                                     |
| Lead-freeProcess Capability   | N/A                                                                                                                                                                 |
| Material Info                 |                                                                                                                                                                     |
| Engineering Number            | 347290201                                                                                                                                                           |
| Reference - Drawing Numbers   |                                                                                                                                                                     |
| Application Specification     | 347290200-AS-CH-000, AS-34729-020-001                                                                                                                               |
| Packaging Specification       | PK-31301-201-001                                                                                                                                                    |
| Product Specification         | PS-34969-100-001                                                                                                                                                    |
| Sales Drawing                 | SD-34969-010-001                                                                                                                                                    |



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

34969 Series

Mates With

34773 , 34772 Stac64 Hybrid Receptacle Connector

Use With

CTX64 Terminal 34803

This document was generated on 07/31/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**