

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0349851606](#)
Status: **Active**
Overview: [MX150 Sealed and Unsealed Connector System](#)
Description: MX150 Hybrid Mat-Sealed Female Connector Assembly, Dual Row, 16 Circuits, Keying Option A, with Connector Position Assurance, Black

Documents:	
Drawing (PDF)	Application Specification AS-33472-100-CH-001 (PDF)
3D Model (PDF)	Packaging Specification PK-30907-895-001 (PDF)
3D Model	Packaging Specification PK-31300-903-001 (PDF)
Product Specification 334760000-PS-CH-000 (PDF)	Datasheet (PDF)
Product Specification PS-33476-000-001 (PDF)	RoHS Certificate of Compliance (PDF)
Application Specification AS-33472-100-001 (PDF)	

General	
Product Family	Crimp Housings
Series	34985
Application	Power, Wire-to-Wire
Comments	With Connector Position Assurance (CPA)
More Detailed Tech Information	http://uscar.org/guest/teams/10/Electrical-Wiring-Component-Applications-Partnership
Overview	MX150 Sealed and Unsealed Connector System
Product Name	MX150
UPC	889056034906
Physical	
Circuits (maximum)	16
Color - Resin	Black
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	SPS/Nylon
Net Weight	24.686/g
Number of Rows	2
Packaging Type	Partitioned Carton
Panel Mount	No
Pitch - Mating Interface	3.50mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +125°C

Material Info

Reference - Drawing Numbers

Application Specification	AS-33472-100-001, AS-33472-100-CH-001
Packaging Specification	PK-30907-895-001, PK-31300-903-001
Product Specification	334760000-PS-CH-000, PS-33476-000-001
Sales Drawing	999-S-016-2-Z02-001, SD-34985-8001-001, SD-34985-8002-001



Series image - Reference only

EU ELV
Compliant

EU RoHS
Compliant
REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free
Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
[34985](#) Series

Mates With
Male Dual Row Hybrid Sealed Connector
[34986](#)

Use With
MX150 Female Terminal [33012](#) , [33001](#)

Industry Standard Terminal 2.80mm