

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0039000082](#)  
**Status:** **Active**  
**Overview:** Mini-Fit Family Power Connectors  
**Description:** Mini-Fit Male Crimp Terminal, Tin (Sn) over Copper Plated Brass, 16 AWG, Bag

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Application Specification 55560001-AS-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-CH-000 (PDF)</a>	<a href="#">Packaging Specification PK-5556-003-001 (PDF)</a>
<a href="#">Product Specification 55560002-PS-ES-000 (PDF)</a>	<a href="#">Test Summary 55560010-TS-000 (PDF)</a>
<a href="#">Product Specification 55560002-PS-SK-000 (PDF)</a>	<a href="#">Test Summary TS-5556-002-001 (PDF)</a>
<a href="#">Product Specification PS-5556-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Product Specification PS-5556-002-001 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	5558
Application	Power, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<a href="#">Mini-Fit Family Power Connectors</a>
Packaging Alternative	<a href="#">39000081 (Reel)</a>
Product Name	Mini-Fit
UPC	800753726802

**Physical**

Durability (mating cycles max)	30
Gender	Male
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	80.000/mg
Packaging Type	Bag
Plating min - Mating	0.889µm
Plating min - Termination	0.889µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.80-3.10mm
Wire Size AWG	16
Wire Size mm <sup>2</sup>	N/A

**Electrical**


Current - Maximum per Contact	9.0A
Voltage - Maximum	600V

**Material Info**

Engineering Number	5558T3L
--------------------	---------

**Reference - Drawing Numbers**

Application Specification	55560001-AS-000
Packaging Specification	PK-5556-003-001
Product Specification	55560002-PS-CH-000, 55560002-PS-ES-000, 55560002-PS-SK-000, PS-5556-001-001, PS-5556-002-001
Sales Drawing	SD-5558XXXX-001, SD-5558XXXX-002
Test Summary	55560010-TS-000, TS-5556-002-001



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[5558 Series](#)

**Use With**

Mini-Fit Jr. Plug Housing [5559](#) <br>Mini-Fit  
BMI Plug Housing [42475](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for Mini-Fit Jr. Terminals	<a href="#">11030044</a>
Hand Crimp Tool for Mini-Fit Jr. Male and Female Crimp Terminals, 16 AWG	<a href="#">2002182200</a>

**Japan**

**Description**

**Product #**

Hand Crimp Tool	<a href="#">570225300</a>
-----------------	---------------------------

New Handtool 570225400  
(Straight Action)  
Hand Extraction Tool 570316000

This document was generated on 07/29/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**