

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0039013069

Status:

Active

Overview:

Mini-Fit Family Power Connectors

Description:

Mini-Fit Jr. Plug Housing, Dual Row, 6 Circuits, UL 94V-0, without Panel Mounting Ears, Natural



Series image - Reference only

Documents:

- [3D Model \(PDF\)](#)
- [3D Model](#)
- [Drawing \(PDF\)](#)
- [Product Specification PS-45750-001-001 \(PDF\)](#)
- [Product Specification PS-5556-001-001 \(PDF\)](#)
- [Application Specification 55560001-AS-000 \(PDF\)](#)
- [Application Specification AS-5557-001-001 \(PDF\)](#)
- [Packaging Specification PK-5559-002-001 \(PDF\)](#)
- [Test Summary 55560010-TS-000 \(PDF\)](#)
- [Test Summary TS-5556-002-001 \(PDF\)](#)
- [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA

UL

LR19980

E29179

General

Product Family

Series

Application

Comments

Crimp Housings

5559

Power, Wire-to-Board, Wire-to-Wire

Current = 13A max. per circuit when header is mated to a receptacle loaded with 45750 series terminals crimped to 16 AWG wire. . See Molex product specification PS-45750-001 for additional current derating information.

Overview

Product Name

UPC

Mini-Fit Family Power Connectors

Mini-Fit Jr.

800753694446

Physical

Breakaway

Circuits (maximum)

Color - Resin

Flammability

Gender

Glow-Wire Capable

Keying to Mating Part

Lock to Mating Part

Material - Resin

Net Weight

Number of Rows

Packaging Type

Panel Mount

Pitch - Mating Interface

Pitch - Termination Interface

Polarized to Mating Part

Stackable

Temperature Range - Operating

No

6

Natural

94V-0

Plug

No

None

Yes

Nylon

1.560/g

2

Bag

No

4.20mm

4.20mm

Yes

No

-40° to +105°C

Electrical

Current - Maximum per Contact

13.0A

Solder Process Data

Lead-freeProcess Capability

N/A

Material Info

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Compliant

Not Contained

Search Parts in this Series

5559 Series

Mates With

Mini-Fit Jr. Receptacle Housing [39012065](#)

Mini-Fit Jr. TPA Cable Assembly [45135](#)

Mini-Fit Jr. Cable Assembly [245135](#)

Use With

Mini-Fit Male Crimp Terminals [5558](#)

Mini-Fit Plus HCS Crimp Terminals
[46012](#)
Mini-Fit Jr. Grounding Pin [30490](#)

Mini-Fit Pre-Crimped Leads [797580005](#)
, [797580013](#)
Mini-Fit Jr. Backshell
[204723](#)

Engineering Number	5559-06P1-210
Reference - Drawing Numbers	
Application Specification	55560001-AS-000, AS-5557-001-001
Packaging Specification	PK-5559-002-001
Product Specification	PS-45750-001-001, PS-5556-001-001
Sales Drawing	55590001-SD-000
Test Summary	55560010-TS-000, TS-5556-002-001

This document was generated on 08/16/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION