

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0393710004

Status: **Active**

Overview: Eurostyle Terminal Blocks

Description: 7.50mm Beau Eurostyle Pluggable PCB Terminal Block, 180° Wire Entry, 4 Circuits

Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

UL E48521

General

Product Family	Terminal Blocks
Series	<u>39371</u>
Application	N/A
Component Type	Plug
Overview	<u>Eurostyle Terminal Blocks</u>
Product Name	Eurostyle Pluggable
Type	Euro Block
UPC	822348040186

Physical

Circuits (Loaded)	4
Entry Angle	180° Angle
Flammability	94V-0
Lock to Mating Part	None
Number of Rows	1
Orientation	Right Angle
PCB Retention	N/A
Panel Mount	No
Pitch - Mating Interface	7.50mm
Pitch - Termination Interface	7.50mm
Polarized to Mating Part	Yes
Stackable	Yes
Temperature Range - Operating	110°C
Wire Size AWG	12, 14, 16, 18, 20, 22, 24, 26, 28, 30
Wire Size mm ²	0.05-2.50

Electrical

Current - Maximum per Contact	15.0A
Voltage - Maximum	300V

Material Info

Engineering Number MX-CIF04003-0N

Reference - Drawing Numbers

Sales Drawing SD-39371-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

**Compliant with
Exemption 6(c)**

REACH SVHC

Contained Per -
D(2020)9139-DC (19
Jan 2021)

Lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

Search Parts in this Series

39371 Series

Mates With

39372 , 39373 Headers

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION