

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **0430300003**  
**Status:** **Active**  
**Overview:** Micro-Fit Connector System  
**Description:** Micro-Fit 3.0 Crimp Terminal, Female, with Select Gold (Au) Plated Phosphor Bronze Contact, 20-24 AWG, Reel

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Test Summary 430450006-TS-000 (PDF)</a>
<a href="#">Product Specification 430450001-PS-KO-000 (PDF)</a>	<a href="#">Test Summary TS-43045-001-001 (PDF)</a>
<a href="#">Product Specification 430450001-PS-SP-000 (PDF)</a>	<a href="#">Test Summary TS-43045-002-001 (PDF)</a>
<a href="#">Product Specification PS-43045-001 (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Packaging Specification PK-43030-001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>
<a href="#">Test Summary 430450005-TS-000 (PDF)</a>	

**General**

Product Family	Crimp Terminals
Series	43030
Application	Power, Wire-to-Board, Wire-to-Wire
Crimp Quality Equipment	Yes
Overview	<u>Micro-Fit Connector System</u>
Packaging Alternative	430300009 (Loose)
Product Name	Micro-Fit 3.0
UPC	800754369169

**Physical**

Gender	Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Net Weight	0.062/g
Packaging Type	Reel
Plating min - Mating	0.762µm
Plating min - Termination	2.540µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	1.85mm max.
Wire Size AWG	20, 22, 24
Wire Size mm <sup>2</sup>	N/A

**Electrical**

Current - Maximum per Contact	8.5A
-------------------------------	------

**Solder Process Data**

Lead-freeProcess Capability	N/A
-----------------------------	-----

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification	PK-43030-001-001
Product Specification	430450001-PS-KO-000, 430450001-PS-SP-000, PS-43045-001
Sales Drawing	SD-43030-XXXX-001
Test Summary	430450005-TS-000, 430450006-TS-000, TS-43045-001-001, TS-43045-002-001



*Series image - Reference only*

**EU ELV**

**Compliant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2021)4569-DC (8  
July 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Compliant

Not Contained

**Search Parts in this Series**

43030 Series

**Use With**

Micro-Fit 3.0 Receptacle Housings [43025](#), [43645](#) <br>Micro-Fit BMI Panel Mount Receptacle Housings [44133](#), [46623](#) <br>Micro-Fit TPA Receptacle Housing [171850](#), [172952](#)

**Application Tooling | FAQ**

*Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.*

**Global**

**Description**

**Product #**

Extraction Tool for Micro-Fit Terminals	<a href="#">11030043</a>
Insertion Tool for Micro-Fit 3.0 and CRC Male and Female Crimp	<a href="#">638120800</a>

Terminals, 20-30  
 AWG  
 PremiumGrade Hand638190000  
 Crimp Tool for Micro-  
 Fit 3.0 Terminals,  
 20-30 AWG  
 FineAdjust Applicator639004500  
 for Insulation OD  
 1.30-1.85mm, 20-24  
 AWG Wire  
 FineAdjust Applicator639018800  
 for Insulation OD  
 1.10-1.30mm - 20-24  
 AWG  
 FineAdjust Applicator639018900  
 for Micro-Fit 3.0  
 Terminals, for 20-24  
 AWG Wire with  
 Insulation Diameter  
 0.91-1.09mm  
 T2 Terminator 639104500  
 for Insulation OD  
 1.30-1.85mm, 20-24  
 AWG  
 T2 Terminator 639118800  
 for insulation OD  
 1.10-1.30mm - 20-24  
 AWG  
 T2 Terminator 639118900  
 for insulation OD  
 0.91-1.09mm - 20-24  
 AWG

**Japan**

<b>Description</b>	<b>Product #</b>
Applicator for M211A Bench Press, 20-30 AWG Wire	<u>572983000</u>
S-1 Applicator for Micro-Fit 3.0 Plug and Receptacle Crimp Terminals, 20-24 AWG	<u>572983700</u>

This document was generated on 08/18/2021

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**