

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0433751001**
Status: **Active**
Overview: Sabre Power Connector
Description: Sabre Double Crimp Terminal, Female, Double 18 AWG, 4.57mm Max. Insulation Diameter, Reel Packaged, Tin (Sn) Plated Brass Contact with TPA

Documents:

Drawing (PDF)	Test Summary 444410000-TS-000 (PDF)
Product Specification PS-44441-9999-001 (PDF)	Datasheet (PDF)
Packaging Specification 433750000-PK-000 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Crimp Terminals
Series	<u>43375</u>
Application	Power, Wire-to-Board, Wire-to-Wire
Comments	For double crimping of 18 AWG wire in a side-by-side orientation. Terminal mates to 3.18mm wide x 0.51mm thick flat blade PC tab. Allows 44441 receptacle housings to comply with the UL1977 finger proof access requirement
Crimp Quality Equipment Overview	Yes
Product Name	<u>Sabre Power Connector</u>
UPC	Sabre 800754365994

Physical

Durability (mating cycles max)	25
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.360/g
Packaging Type	Reel
Plating min - Mating	0.508µm
Plating min - Termination	0.508µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.57mm max.
Wire Size AWG	14, 16, 18+18
Wire Size mm ²	N/A

Electrical

Current - Maximum per Contact	18.0A
Voltage - Maximum	600V

Solder Process Data

Lead-free Process Capability	N/A
------------------------------	-----

Material Info

Reference - Drawing Numbers

Packaging Specification	433750000-PK-000
Product Specification	PS-44441-9999-001
Sales Drawing	SD-43375-1001-001
Test Summary	444410000-TS-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

43375 Series

Use With

44441 Receptacle Housings

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
PremiumGrade Hand Crimp Tool for Sabre Female Terminals 14-18 AWG or Double 18 AWG (vertical)	<u>638117300</u>
Extraction and Activation Tool	<u>638132700</u>
Terminator Die - Doubles	<u>638405200</u>
Mini-Mac Applicator	<u>638916100</u>

Mini-Mac Applicator, [638917000](#)
For Narrow
Insulation Crimp

This document was generated on 08/18/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION