


PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: 0451320603
Status: Active
Overview: Micro-Fit Connector System
Description: Micro-Fit TPA-to-Micro-Fit TPA Off-the-Shelf (OTS) Cable Assembly, Dual Row, 300.00mm Length, 6 Circuits, Black



Series image - Reference only

Documents:
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General
Product Family Cable Assemblies
Series 45132
Application Power, Wire-to-Board, Wire-to-Wire
Assembly Configuration Dual Ended Connectors
Connector to Connector Micro-Fit TPA Both Ends
Overmolded No
Overview Micro-Fit Connector System
Product Name Micro-Fit TPA
Type Discrete Wire Assembly
UPC 889056745253

Physical
Cable Length 300.00mm
Circuits (Loaded) 6
Color - Resin Black
Gender Female-Female
Lock to Mating Part Yes
Material - Metal Phosphor Bronze
Material - Plating Mating Tin
Material - Plating Termination Tin
Material - Resin Nylon
Net Weight 16.468/g
Number of Rows 2
Packaging Type Bag
Pitch - Mating Interface 3.00mm
Plating min - Mating 1.016µm
Plating min - Termination 1.016µm
Single Ended No
Termination Interface: Style Crimp or Compression
Wire Insulation Diameter 1.76mm
Wire Size AWG 20
Wire/Cable Type UL 1007

Electrical
Current - Maximum per Contact 5.0A
Voltage - Maximum 300V

Material Info

Reference - Drawing Numbers
Sales Drawing 2012341032-000

EU ELV
Not Relevant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)
Halogen-Free
Status
Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
45132 Series

Mates With
Micro-Fit 3.0 Headers 43045
Micro-Fit
3.0 Plug Housings 43020 , 203632