

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0473460001**
Status: **Active**
Overview: USB Products and Solutions
Description: Micro-USB B Receptacle with Flange, Bottom Mount, Surface Mount, Lead-Free

Documents:

| | |
|--------------------------------|----------------------------------------------------------------|
| 3D Model | Product Specification PS-47346-001-001 (PDF) |
| Drawing (PDF) | Packaging Specification PK-47346-001-001 (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

UL E107635

General


| | |
|----------------|-------------------------------------------|
| Product Family | I/O Connectors |
| Series | 47346 |
| Application | Wire-to-Board |
| Comments | Signal contacts 1.0A, Power contacts 1.8A |
| Component Type | Receptacle |
| Overview | <u>USB Products and Solutions</u> |
| Product Name | USB |
| Standard | USB 2.0 |
| Type | Micro-B |
| UPC | 822350955478 |

Physical

| | |
|--------------------------------|--------------------------------|
| Circuits (Loaded) | 5 |
| Circuits (maximum) | 5 |
| Color - Resin | Black |
| Durability (mating cycles max) | 10000 |
| Flammability | 94V-0 |
| Gender | Female |
| Keying to Mating Part | Yes |
| Lock to Mating Part | No |
| Material - Metal | Copper Alloy |
| Material - Plating Mating | Gold |
| Material - Plating Termination | Gold |
| Material - Resin | High Temperature Thermoplastic |
| Mounting Style | Bottom-Mount |
| Net Weight | 0.247/g |
| Number of Rows | 1 |
| Orientation | Right Angle |
| PCB Retention | None |
| Packaging Type | Embossed Tape on Reel |
| Panel Mount | No |
| Pitch - Mating Interface | 0.65mm |
| Pitch - Termination Interface | 0.65mm |
| Polarized to Mating Part | Yes |
| Ports | 1 |
| Surface Mount Compatible (SMC) | Yes |
| Temperature Range - Operating | -30° to +85°C |
| Termination Interface: Style | Surface Mount |
| Waterproof / Dustproof | No |

Electrical

| | |
|-------------------------------|------------|
| Current - Maximum per Contact | 1.8A, 1.0A |
| Grounding to Panel | Yes |



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

47346 Series

| | |
|-------------------|--------------|
| Shield Type | Full Shield |
| Shielded | Yes |
| Voltage - Maximum | 30V AC (RMS) |

Solder Process Data

| | |
|------------------------------------------------|--------|
| Duration at Max. Process Temperature (seconds) | 010 |
| Lead-free Process Capability | REFLOW |
| Max. Cycles at Max. Process Temperature | 001 |
| Process Temperature max. C | 260 |

Material Info**Reference - Drawing Numbers**

| | |
|-------------------------|------------------|
| Packaging Specification | PK-47346-001-001 |
| Product Specification | PS-47346-001-001 |
| Sales Drawing | SD-47346-001-001 |

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION