



- NOTE :
- MATERIAL :  
 HOUSING : LCP, BLACK, UL94V-0  
 TERMINAL : COPPER ALLOY THICKNESS = 0.15 MM  
 SHIELD CASE : STAINLESS STEEL THICKNESS = 0.30 MM
  - PLATING :  
 TERMINAL:  
 CONTACT AREA : GOLD FLASH OVER MINIMUM 0.75 MICRON Pd/Ni.  
 SOLDER TAIL AREA : GOLD FLASH.  
 UNDER PLATING : NICKEL 2.0 MICRON MINIMUM.  
 SHIELD :  
 MATTE TIN 3.8 MICRON MINIMUM.  
 UNDER PLATING : NICKEL 1.27 MICRON MINIMUM.
  - TAIL & NAIL COPLANARITY 0.08 mm MAXIMUM.
  - PACKAGING SPECIFICATION : PK-47491-001
  - PRODUCT SPECIFICATION : PS-47642-001



THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC: REVISED						<b>molex</b>		
mm		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)										MICRO USB B REC. MIDDLE MOUNT ASS'Y		
ANGULAR TOL ± 3.0°												
4 PLACES		±		EC NO: 616089		2019/04/23		PRODUCT CUSTOMER DRAWING				
3 PLACES		±		DRWN: MGLEI		2019/04/25						
2 PLACES		± 0.25		CHK'D: XQZHANG		2019/04/25						
1 PLACE		± 0.25		APPR: XQZHANG		2019/04/25		DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION
0 PLACES		±		INITIAL REVISION:		2006/06/06		SD-47491-001		PSD	001	H
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
		A3-SIZE		47491		47491-0001		GENERAL MARKET		1 OF 1		