

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0477450100](#)
Status: **Active**
Overview:
Description: 2.50mm, 3.50mm CMC Header, Right-Angle, 28 Position, 1 Port, Black, Peg, Lead-Free

General

Product Family	PCB Headers
Series	47745
Application	Automotive, Power, Wire-to-Board
Comments	Coding: Black
Overview	cmc_connectors
Product Name	CMC
UPC	887191161006

Physical

Breakaway	No
Circuits (Loaded)	28
Circuits (maximum)	28
Circuits Detail	5x 2.8mm, 5 x 1.5mm, 18 x 0.635mm terminals
Color - Resin	Black
Durability (mating cycles max)	20
First Mate / Last Break	Yes
Glow-Wire Capable	No
Guide to Mating Part	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	36.292/g
Number of Rows	4
Orientation	Right Angle
PC Tail Length	2.90mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Carton
Pitch - Mating Interface	2.50mm, 3.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Closed Ends
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Solder or Weld

Electrical

Current - Maximum per Contact	12.0A, 2.5A, 21.0A
Voltage - Maximum	14V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	010
Lead-free Process Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

EU ELV
Compliant

EU RoHS **China RoHS**
Compliant

REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free
Status

Low-Halogen
For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[47745](#) Series

Mates With

CMC Receptacle [64318](#)

Use With

[64318](#) CMC Female, [64322](#) CP 0.6, [64323](#) CP 1.5, [64324](#) CP 2.8, [64320-1301](#) Wire Cap, [64325](#) Blind Plugs

Material Info

Reference - Drawing Numbers

Packaging Specification
Sales Drawing

PK-47745-001-001
SD-47745-100-001

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION