

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5015681007

Status:

Active

Overview:

Pico-Clasp Wire-to-Board Connectors

Description:

1.00mm Pitch, Pico-Clasp PCB Header, Single Row, Right-Angle, Surface Mount, Tin Plated, Inner Positive Lock, 10 Circuits, Natural

Documents:	
3D Model (PDF)	Product Specification 5013301000-PS-001 (PDF)
Drawing (PDF)	Application Specification 5013300000-AS-000 (PDF)
3D Model	Packaging Specification SPK-501568-001-001 (PDF)
Product Specification 5013300000-PS-001 (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	PCB Headers
Series	501568
Application	Signal, Wire-to-Board
Overview	Pico-Clasp Wire-to-Board Connectors
Product Name	Pico-Clasp
UPC	822348871865

Physical	
Breakaway	No
Circuits (Loaded)	10
Circuits (maximum)	10
Color - Resin	Natural
Durability (mating cycles max)	30
First Mate / Last Break	No
Glow-Wire Capable	No
Lock to Mating Part	Yes
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Nylon
Net Weight	213.200/mg
Number of Rows	1
Orientation	Right Angle
PCB Locator	No
PCB Retention	Yes
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Polarized to Mating Part	Yes
Polarized to PCB	No
Shrouded	Fully
Stackable	No
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Surface Mount

Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	100V AC (RMS)/DC

Material Info

Reference - Drawing Numbers	
Application Specification	5013300000-AS-000



Series image - Reference only

EU ELV	
Compliant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
501568 Series

Mates With
501330 Pico-Clasp Wire-to-Board Female Housing

Packaging Specification
Product Specification
Sales Drawing

SPK-501568-001-001
5013300000-PS-001, 5013301000-PS-001
5015680000-SD-000

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION