

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [5017843008](#)
Status: **Active**
Overview: [Easy-On FFC FPC Connectors](#)
Description: 0.50mm Pitch FFC-to-Board Plug Jacket Cover, with Ground Type, 30 Circuits

Documents:
[3D Model](#)
[Drawing \(PDF\)](#)
[3D Model \(PDF\)](#)
[Product Specification PS-501864-004-001 \(PDF\)](#)
[Application Specification 5017832000-A00 \(PDF\)](#)
[Packaging Specification SPK-501784-001-001 \(PDF\)](#)
[RoHS Certificate of Compliance \(PDF\)](#)


Agency Certification
UL E29179

General
Product Family Accessories
Series [501784](#)
Comments Requires a custom FFC with notches
Component Type Jacket Cover
Overview [Easy-On FFC FPC Connectors](#)
Product Name Easy-On
UPC 822350718608

Physical
Breakaway No
Circuits (Loaded) 30
Circuits (maximum) 30
Color - Resin Black
Flammability 94V-0
Gender Plug
Material - Resin Polyester
Net Weight 149.500/mg
Packaging Type Bag
Polarized to Mating Part Yes
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers
Application Specification 5017832000-A00
Packaging Specification SPK-501784-001-001
Product Specification PS-501864-004-001
Sales Drawing SD-501784-005-001



EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[501784](#) Series

Use With
[501786](#) FFC-to-Board Connector, [501864](#) FFC-to-Board Connector, [501783](#) Plug Jacket