

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

5023510800

Status:

Active

Overview:

Description:

DuraClik Wire-to-Board Receptacle Housing, Single Row, 8 Circuits, Natural

General	
Product Family	Crimp Housings
Series	502351
Application	Automotive, Signal, Wire-to-Board
Comments	Molex part has an inner-locking system versus an outer-locking system. Molex part with tail protection feature.
Overview	duraclik
Product Name	DuraClik
UPC	800756666877
Physical	
Circuits (maximum)	8
Color - Resin	Natural
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Net Weight	328.000/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	2.00mm
Polarized to Mating Part	Yes
Temperature Range - Operating	-40° to +105°C
Electrical	
Current - Maximum per Contact	3.0A
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Packaging Specification	PK-502351-001-001
Product Specification	PS-502351-001-001, PS-502351-002-001
Sales Drawing	SD-502351-001-001

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

China RoHS

Green Image

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Compliant

Not Contained

Search Parts in this Series

502351 Series

Mates With

DuraClik Header 560020 , 502352

Use With

Tin-Plated Crimp Terminal AWG 22-26
560085
 Tin-Plated Crimp Terminal
AWG 24-30 50212
 Gold-Plated Crimp
Terminal AWG 22-26 56161
 DuraClik
Pre-Crimped Leads 797581008 , 797581009

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION