

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0510210600

Status:


Active

Overview:

PicoBlade Connector System

Description:

1.25mm Pitch, PicoBlade Receptacle Crimp Housing, Single Row, Friction Lock, 6 Circuits, Natural



Documents:	
Drawing (PDF)	Product Specification 510211024-PS-000 (PDF)
2D Drawing DXF (PDF)	Product Specification PS-51021-009-001 (PDF)
3D Model (PDF)	Product Specification PS-51021-010-001 (PDF)
3D Model	Product Specification PS-51021-024-001 (PDF)
2D Drawing (DXF)	Product Specification PS-51021-025-001 (PDF)
Product Specification 510210000-PS-000 (PDF)	Product Specification PS-51021-026-001 (PDF)
Product Specification 510210001-PS-000 (PDF)	Product Specification PS-51021-027-001 (PDF)
Product Specification 510210006-PS-000 (PDF)	Application Specification 510210000-AS-000 (PDF)
Product Specification 510211000-PS-000 (PDF)	Application Specification 510210001-AS-000 (PDF)
Product Specification 510211001-PS-000 (PDF)	Packaging Specification SPK-51021-001-001 (PDF)
Product Specification 510211009-PS-000 (PDF)	RoHS Certificate of Compliance (PDF)
Product Specification 510211010-PS-000 (PDF)	

Agency Certification	
CSA	LR19980
UL	E29179
General	
Product Family	Crimp Housings
Series	51021
Application	Signal, Wire-to-Board, Wire-to-Wire
Current Derating Order No	987651-3691
Overview	PicoBlade Connector System
Product Name	PicoBlade
UPC	800753750456
Physical	
Circuits (maximum)	6
Color - Resin	Natural
Flammability	94V-0
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	58.250/mg
Number of Rows	1
Packaging Type	Bag
Panel Mount	No
Pitch - Mating Interface	1.25mm
Polarized to Mating Part	Yes
Stackable	No
Temperature Range - Operating	-40° to +105°C
Material Info	
Reference - Drawing Numbers	
Application Specification	510210000-AS-000, 510210001-AS-000
Packaging Specification	SPK-51021-001-001
Product Specification	510210000-PS-000, 510210001-PS-000, 510210006-PS-000, 510211000-PS-000, 510211001-PS-000,

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - D(2020)9139-DC (19 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image

ELV

Compliant

RoHS Phthalates

Not Contained

Search Parts in this Series

51021 Series

Mates With

PicoBlade Header [53261](#) , [53047](#) , [53398](#) , [53048](#) . PicoBlade Plug Housing [51047](#)

Use With

PicoBlade Crimp Terminal [50058](#) , [50079](#) . PicoBlade Pre-Crimped Lead [214920](#) , [214921](#) , [797580006](#) , [797580014](#) , [797581059](#) , [797581060](#) , [797581061](#) , [797581062](#) , [797581063](#)

Sales Drawing

510211009-PS-000, 510211010-PS-000, 510211024-
PS-000, PS-51021-009-001, PS-51021-010-001,
PS-51021-024-001, PS-51021-025-001,
PS-51021-026-001, PS-51021-027-001
SD-51021-002-001, SD-51021-005-001

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION