

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0528080871

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

1.00mm Pitch Easy-On FFC/FPC Connector, Surface Mount, Vertical, Non-ZIF, Tin (Sn) Plating, with Pick-and-Place Polyimide Tape, 8 Circuits



Documents:	
3D Model	Product Specification PS-52808-004-001 (PDF)
3D Model (PDF)	Packaging Specification 528089200-200 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
UL	E29179
General	
Product Family	FFC/FPC Connectors
Series	52808
Overview	Easy-On FFC FPC Connectors
Product Name	Easy-On
UPC	822348136506
Physical	
Actuator Type	Non-ZIF
Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Natural
Contact Position	N/A
Durability (mating cycles max)	10
Mated Height	5.05mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin-Bismuth
Material - Plating Termination	Tin-Bismuth
Material - Resin	High Temperature Thermoplastic
Net Weight	243.800/mg
Number of Rows	1
Orientation	Vertical
PCB Locator	No
PCB Mounting	Surface Mount
PCB Retention	None
Packaging Type	Embossed Tape on Reel
Pitch - Mating Interface	1.00mm
Pitch - Termination Interface	1.00mm
Polarized to PCB	No
Stackable	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-20° to +80°C
Wire/Cable Type	FFC/FPC
Electrical	
Current - Maximum per Contact	0.5A
Voltage - Maximum	125V
Material Info	
Reference - Drawing Numbers	
Packaging Specification	528089200-200
Product Specification	PS-52808-004-001
Sales Drawing	SD-52808-025, SD-52808-025-001, SD-52808-026

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

52808 Series

This document was generated on 07/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION