

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0545482271

Status:

Active

Overview:

Easy-On FFC FPC Connectors

Description:

0.50mm Pitch Easy-On FFC/FPC Connector, 1.20mm Height, Right-Angle, Surface Mount, ZIF, Bottom Contact Style, 22 Circuits, Gold (Au)Plating

Documents:

- Drawing (PDF)

3D Model

3D Model (PDF)

Product Specification PS-54548-039-001 (PDF)
- Application Specification AS-54548-001-001 (PDF)

Packaging Specification SPK-54548-001-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

UL

E29179

General

Product Family

Series

Overview

Product Name

UPC

FFC/FPC Connectors

54548

Easy-On FFC FPC Connectors

Easy-On

822348231249

Physical

Actuator Type

Circuits (Loaded)

Contact Position

Durability (mating cycles max)

Mated Height

Material - Metal

Material - Plating Mating

Material - Plating Termination

Net Weight

Number of Rows

Orientation

PCB Locator

PCB Mounting

PCB Retention

Packaging Type

Pitch - Mating Interface

Polarized to PCB

Stackable

Temperature Range - Operating

Wire/Cable Type

Slider

22

Bottom

20

1.20mm

Phosphor Bronze

Gold

Tin

108.716/mg

1

Right Angle

No

Surface Mount

Yes

Embossed Tape on Reel

0.50mm

Yes

No

-20° to +85°C

FFC/FPC

Electrical

Current - Maximum per Contact

Voltage - Maximum

0.5A

50V

Material Info

Reference - Drawing Numbers

Application Specification

Packaging Specification

Product Specification

Sales Drawing

AS-54548-001-001

SPK-54548-001-001

PS-54548-039-001

SD-54548-039-001, SD-54548-040-001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

Green Image

Not Relevant

Not Contained

Search Parts in this Series

54548 Series

This document was generated on 07/26/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION