

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0638193400](#)
Status: **Active**
Overview: [Application Tooling](#)
Description: Hand Crimp Tool for CP 2.8 Receptacle 18-20 AWG Type TXL Wire and 0.50-0.75mm² Type ID & ID Wire with 2.80mm, CMC Wire Seal Receptacle

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Application Tooling
Series [207129](#)
Comments Field Repair, See Tooling Specification (PDF) Above.
Type: 4A
Function Crimp
Geographic Area Global
Level of Automation Manual
More Detailed Tech Information [applicationtooling@molex.com](#)
Overview [Application Tooling](#)
Product Name PremiumGrade
Tool Type Hand Crimp Tool
UPC 883906383831
Warranty Disclaimer CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified.

Physical
Net Weight 428.885/zg

Material Info

Reference - Drawing Numbers
[Application Tooling Documents](#)
ATS-6381934HM-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



Series image - Reference only

EU ELV
Not Relevant

EU RoHS Compliant REACH SVHC Not Contained Per - ED/61/2018 (27 June 2018) Halogen-Free Status Not Relevant For more information, please visit Contact US	China RoHS China ROHS Not Relevant ELV Not Relevant RoHS Phthalates Not Contained
--	---

Search Parts in this Series
[207129](#) Series

Use With
Battery Powered Crimping Tool [638160200](#), [638160250](#), Air Powered Crimping Tool [638160100](#)

Application Tooling Description	FAQ Product #
2.80mm, CMC CP Female Terminal, Tin plated, for Tab Dimensions 2.80mm by 0.80mm, Wire Size 0.50-1.00mm ²	643241049
2.80mm, CMC CP Female Terminal, Tin plated, Selective 1.27µm Gold in Contact Area, for Tab Dimensions 2.80mm by 0.80mm, Wire Size 0.50-1.00mm ²	643241149

This document was generated on 07/30/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION