

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0643191219

Status:

Active

Overview:

CMC and CMX Sealed, Hybrid, Modular Connectors

Description:

.635mm, 1.50mm, CMC Receptacle, 32 Circuits, Left Wire Output, Brown Coding, Mat Sealed



Documents:	
3D Model	Application Specification AS-64319-002-SP-001 (PDF)
Drawing (PDF)	Application Specification AS-98420-002-001 (PDF)
3D Model (PDF)	Application Specification AS-98420-002-CH-001 (PDF)
Product Specification PS-64319-001-001 (PDF)	Application Specification AS-98420-002-FR-001 (PDF)
Product Specification PS-64319-002-001 (PDF)	Application Specification AS-98420-002-SP-001 (PDF)
Application Specification AS-64319-002-001 (PDF)	Packaging Specification PK-64319-001-001 (PDF)
Application Specification AS-64319-002-CH-001 (PDF)	Datasheet (PDF)
Application Specification AS-64319-002-FR-001 (PDF)	RoHS Certificate of Compliance (PDF)

Application tooling part link	
Application Tooling Part Link	63812-1100
Application Tooling Part Link	63824-1200
General	
Product Family	Crimp Housings
Series	64319
Application	Automotive, Power, Wire-to-Board
Comments	Current tested on a 5 terminals loaded connector, current for temperature increase of 40°C . Current max = 6.0A for 0.635mm Terminal (0.75mm² wire) and 12.0A for 1.50mm Terminal (2.00mm² wire)
More Detailed Tech Information	Sealed, high-density, modular connecting system for Power Train and Body Electronics applications in cars, trucks, busses
Overview	CMC and CMX Sealed, Hybrid, Modular Connectors
Product Name	CMC
UPC	883906129767
Physical	
Circuits (maximum)	32
Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Color - Resin	Brown
Gender	Receptacle
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Resin	Polyester
Net Weight	29.426/g
Number of Rows	4
Packaging Type	Carton
Panel Mount	No
Pitch - Mating Interface	2.54mm, 3.70mm
Polarized to Mating Part	Yes
Stackable	No

EU ELV
Compliant

EU RoHS
Compliant

REACH SVHC
Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free
Status
Low-Halogen

For more information, please visit [Contact US](#)

China RoHS

Green Image
ELV
RoHS Phthalates

Compliant
Not Contained

Search Parts in this Series

64319 Series

Mates With

32-Circuit CMC Header [643340300](#)

Use With

CMC CP Terminals [64322](#) (0.635mm), [64323](#) (1.50mm) . CMC Wire Cap [643191201](#) . Sealing Plugs [643251010](#) , [643251023](#)

Application Tooling FAQ	
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.	
Global	
Description	Product #
Continuity Test Pen Assembly	638121100
Unlocking Tool for CMC and	638241200

Temperature Range - Operating	-40° to +125°C	CMX Receptacle Connector
Electrical		
Current - Maximum per Contact	12.0A, 2.5A	
Solder Process Data		
Lead-freeProcess Capability	N/A	
Material Info		
Reference - Drawing Numbers		
Application Specification	AS-64319-002-001, AS-64319-002-CH-001, AS-64319-002-FR-001, AS-64319-002-SP-001, AS-98420-002-001, AS-98420-002-CH-001, AS-98420-002-FR-001, AS-98420-002-SP-001	
Packaging Specification	PK-64319-001-001	
Product Specification	PS-64319-001-001, PS-64319-002-001	
Sales Drawing	SD-64319-001-001	

This document was generated on 07/28/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION