

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0643340300](#)
Status: **Active**
Overview: CMC and CMX Sealed, Hybrid, Modular Connectors
Description: 2.50mm, 3.70mm CMC Header, Right-Angle, 32 Circuits, 1 Port, Brown

Documents:

Drawing (PDF)	Datasheet (PDF)
3D Model (PDF)	RoHS Certificate of Compliance (PDF)
3D Model	

General

Product Family	PCB Headers
Series	64334
Application	Automotive, Board-to-Board, Wire-to-Board
Comments	Coding: Brown
Overview	<u>CMC and CMX Sealed, Hybrid, Modular Connectors</u>
Product Name	CMC
UPC	883906844448

Physical

Breakaway	No
Circuits (Loaded)	32
Circuits (maximum)	32
Circuits Detail	8 x 1.5mm & 24 x 0.635mm terminals
Color - Resin	Black
Durability (mating cycles max)	20
First Mate / Last Break	No
Glow-Wire Capable	No
Guide to Mating Part	Yes
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Tin
Material - Resin	Nylon Alloy
Net Weight	28.860/g
Number of Rows	4
Orientation	Right Angle
Packaging Type	Tray
Pitch - Mating Interface	2.50mm, 3.70mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Temperature Range - Operating	-40° to +105°C
Termination Interface: Style	Solder or Weld

Electrical

Current - Maximum per Contact	12.0A, 2.5A
Voltage - Maximum	14V DC

Solder Process Data

Duration at Max. Process Temperature (seconds)	020
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001
Process Temperature max. C	260

Material Info



Series image - Reference only

EU ELV

Compliant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS	Green Image
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series

[64334 Series](#)

Mates With

CMC Receptacle Housing [643193219](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION