

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0672983090**
Status: **Active**
Overview: USB Products and Solutions
Description: Universal Serial Bus (USB) Shielded I/O Receptacle, Right-Angle, Dual Stacked, Type A, Gold (Au) Flash, Black Housing, with 4 Beveled Metal Pins, Lead-Free

Documents:

3D Model	Packaging Specification PK-67298-003-001 (PDF)
3D Model (PDF)	Test Summary TS-67298-008-001 (PDF)
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

General


Product Family	I/O Connectors
Series	<u>67298</u>
Application	Wire-to-Board
Comments	4 Beveled Metal Pins
Component Type	Receptacle
Overview	<u>USB Products and Solutions</u>
Product Name	USB
Standard	USB 2.0
Type	A
UPC	822350050692

Physical

Circuits (Loaded)	8
Circuits (maximum)	8
Color - Resin	Black
Gender	Female
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Mounting Style	Top-Mount
Net Weight	8.671/g
Number of Rows	2
Orientation	Right Angle
PC Tail Length	2.80mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Panel Mount	Yes
Pitch - Mating Interface	2.00mm, 2.50mm
Pitch - Termination Interface	2.00mm, 2.50mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Ports	2
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	0° to +50°C
Termination Interface: Style	Through Hole
Waterproof / Dustproof	No

Electrical

Current - Maximum per Contact	1.5A
Shield Type	Full Shield
Shielded	Yes
Voltage - Maximum	30V DC



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2021)4569-DC (8
July 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[67298 Series](#)

Mates With

USB Type A Plug

Solder Process Data

Lead-free Process Capability
Process Temperature max. C

WAVE
260

Material Info**Reference - Drawing Numbers**

Packaging Specification
Product Specification
Sales Drawing
Test Summary

PK-67298-003-001
RPS-67298-001-001
SD-67298-008-001
TS-67298-008-001

This document was generated on 08/23/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION