

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0701070008

Status:

Active

Overview:

SL Modular Connectors

Description:

SL Wire-to-Wire Crimp Housing, Single Row, Version A, without Mounting Ears, 9 Circuits, Black



Series image - Reference only

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

Product Specification PS-70400-001 (PDF)

Packaging Specification PK-70107-100-001 (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification		
CSA	LR19980	
UL	E29179	
General		
Product Family	Crimp Housings	
Series	70107	
Application	Signal, Wire-to-Wire	
Comments	Version A without Mounting Ears	
Overview	SL Modular Connectors	
Product Name	SL	
UPC	800753560833	
Physical		
Circuits (maximum)	9	
Color - Resin	Black	
Flammability	94V-0	
Gender	Plug	
Glow-Wire Capable	No	
Lock to Mating Part	Yes	
Material - Resin	Polyester	
Net Weight	1.645/g	
Number of Rows	1	
Packaging Type	Bag	
Panel Mount	No	
Pitch - Mating Interface	2.54mm	
Polarized to Mating Part	Yes	
Stackable	No	
Temperature Range - Operating	-40° to +105°C	
Material Info		
Reference - Drawing Numbers		
Packaging Specification	PK-70107-100-001	
Product Specification	PS-70400-001	
Sales Drawing	SD-70107-0001-0024-001	

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2021)4569-DC (8 July 2021)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

70107 Series

Mates With

SL Crimp Housing Versions A, G and D Only

70066 (Version C and H will not mate to the 70107 housing series) . SL Insulation Displacement Connector Assembly, Version G Housing 70400 . SL Single Row Receptacle, Version G 70430

Use With

70021 SL Crimp Terminal

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION