

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0701070046](#)
Status: **Active**
Overview: [SL Modular Connectors](#)
Description: SL Wire-to-Wire Panel Mount Crimp Housing, Single Row, Version B, with Mounting Ears, 12 Circuits, Black

Documents:
[Drawing \(PDF\)](#) [Product Specification PS-70400-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-70107-100-001 \(PDF\)](#)
[3D Model](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification
CSA LR19980
UL E29179

General
Product Family Crimp Housings
Series [70107](#)
Application Signal, Wire-to-Wire
Comments Version B with Mounting Ears
Overview [SL Modular Connectors](#)
Product Name SL
UPC 800754347273

Physical
Circuits (maximum) 12
Color - Resin Black
Flammability 94V-0
Gender Plug
Glow-Wire Capable No
Lock to Mating Part None
Material - Resin Polyester
Net Weight 2.685/g
Number of Rows 1
Packaging Type Bag
Panel Mount Yes
Pitch - Mating Interface 2.54mm
Polarized to Mating Part Yes
Stackable No
Temperature Range - Operating -40° to +105°C

Material Info

Reference - Drawing Numbers
Packaging Specification PK-70107-100-001
Product Specification PS-70400-001
Sales Drawing SD-70107-0036-0059-001



Series image - Reference only

EU ELV
Compliant

EU RoHS **China RoHS**
Compliant
REACH SVHC
Not Contained Per -
D(2021)4569-DC (8
July 2021)
Halogen-Free
Status
Not Low-Halogen
For more information, please visit [Contact US](#)

China ROHS Green Image
ELV Compliant
RoHS Phthalates Not Contained

Search Parts in this Series
[70107 Series](#)

Mates With
SL Crimp Housing Versions A, G and D Only
[70066](#) (Version C and H will not mate to
the 70107 housing series) . SL Insulation
Displacement Connector Assembly,
Version G Housing [70400](#) . SL Single Row
Receptacle, Version G [70430](#)

Use With
[70021](#) SL Crimp Terminal