

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0732511850

Status:

Active

Overview:

Precision Compression-Mount Microwave Test Connectors

Description:

50 Ohms, Precision Test Connector, Optimized SMA Jack, Two Hole Flange, Pressure Contact for Test Boards, Tray



Series image - Reference only

Documents:	
3D Model (PDF)	3D Model
Drawing (PDF)	RoHS Certificate of Compliance (PDF)
HFSS Model	

General	
Product Family	RF/Coax Connectors
Series	73251
Comments	EMI/RFI grounding ring
Overview	Precision Compression-Mount Microwave Test Connectors
Product Name	Optimized SMA
Style	PCB
Type	Subminiature
UPC	756054753262
Wire/Cable Type	N/A
Physical	
Gender	Jack
Keying to Mating Part	None
Net Weight	1.800/g
Orientation	Straight
PCB Mounting	Surface Mount
Packaging Type	Tray
Panel Mount	Yes
Panel Mount Method	Flange
Reverse Polar	No
Electrical	
Frequency	27 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 500 Vrms@Sea Level
Solder Process Data	
Lead-freeProcess Capability	N/A
Material Info	
Reference - Drawing Numbers	
Sales Drawing	SD-73251-185-000, SD-73251-348-000

EU ELV	
Compliant with Exemption 3	
EU RoHS	China RoHS
Compliant with Exemption 6(c)	
REACH SVHC	
Contained Per - D(2021)4569-DC (8 July 2021)	
Lead	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	50 Image
ELV	Compliant with Exemption 3
RoHS Phthalates	Not Contained

Search Parts in this Series
[73251](#) Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION