

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

**Part Number:** [0732520091](#)  
**Status:** **Active**  
**Overview:** [Precision Compression-Mount Microwave Test Connectors](#)  
**Description:** 50 Ohms, Precision Test Connector, 2.92mm PCB Jack, Field Replaceable, 2 Hole Flange, with 2 Screws 6.35mm, PCB Thickness 1.78-4.19mm

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[HFSS Model](#)

**General**

|                 |                                                                       |
|-----------------|-----------------------------------------------------------------------|
| Product Family  | RF/Coax Connectors                                                    |
| Series          | <a href="#">73252</a>                                                 |
| Overview        | <a href="#">Precision Compression-Mount Microwave Test Connectors</a> |
| Product Name    | 2.92mm                                                                |
| Style           | PCB                                                                   |
| Type            | Subminiature                                                          |
| UPC             | 884982956025                                                          |
| Wire/Cable Type | N/A                                                                   |

**Physical**

|                       |               |
|-----------------------|---------------|
| Cable Attachment      | N/A           |
| Gender                | Jack          |
| Keying to Mating Part | None          |
| Net Weight            | 1.888/g       |
| Orientation           | Straight      |
| PCB Mounting          | Surface Mount |
| Packaging Type        | Tray          |
| Panel Mount           | No            |
| Panel Mount Method    | Compression   |
| Reverse Polar         | No            |

**Electrical**

|                 |                             |
|-----------------|-----------------------------|
| Frequency       | 40 GHz                      |
| Impedance       | 50Ω                         |
| Power / Voltage | VOLTAGE: 500 Vrms@Sea Level |

**Solder Process Data**

|                             |     |
|-----------------------------|-----|
| Lead-freeProcess Capability | N/A |
|-----------------------------|-----|

**Material Info**

**Reference - Drawing Numbers**

|               |                  |
|---------------|------------------|
| Sales Drawing | SD-73252-009-000 |
|---------------|------------------|



Series image - Reference only

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per -  
D(2020)9139-DC (19  
Jan 2021)  
lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

**China RoHS**

|                 |               |
|-----------------|---------------|
| China ROHS      | 50 Image      |
| ELV             | Not Relevant  |
| RoHS Phthalates | Not Contained |

**Search Parts in this Series**

[73252 Series](#)