

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0733660061

Status:

Active

Overview:

MCX RF Connectors

Description:

50 Ohms, MCX Jack Receptacle, Vertical, Straight, 7.10mm Height, 1.57mm Standoff Height, Gold (Au) Plated Body, Tray

Documents:

3D Model

Drawing (PDF)

3D Model (PDF)

RoHS Certificate of Compliance (PDF)

General

Product Family

Series

Overview

Product Name

Style

Type

UPC

Wire/Cable Type

RF/Coax Connectors

73366

MCX RF Connectors

MCX

PCB

Microminiature

800756205649

N/A

Physical

Gender

Keying to Mating Part

Net Weight

Orientation

PCB Mounting

PCB Thickness - Recommended

Packaging Type

Panel Mount

Panel Mount Method

Reverse Polar

Jack

None

0.560/g

Straight

Through Hole

1.20mm

Tray

No

N/A

No

Electrical

Frequency

Impedance

Power / Voltage

6 GHz

50Ω

VOLTAGE: 335 Vrms@Sea Level

Solder Process Data

Duration at Max. Process Temperature (seconds)

Lead-freeProcess Capability

Max. Cycles at Max. Process Temperature

Process Temperature max. C

010

REFLOW

002

260

Material Info

Reference - Drawing Numbers

Sales Drawing

SD-73366-006-001, SD-73366-619-000



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

50 Image

Not Relevant

Not Contained

Search Parts in this Series

73366 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION