

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0734151252](#)  
**Status:** **Active**  
**Overview:** MMCX RF Connectors  
**Description:** 50 Ohms, MMCX Plug RG-174, RG-188 and RG-316 Cable, Plating Per Commercial Requirements, One Piece Per Bag

**Documents:**

[3D Model](#) [Application Specification 735970550-000 \(PDF\)](#)  
[3D Model \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)  
[Drawing \(PDF\)](#)

**General**

Product Family	RF/Coax Connectors
Series	<a href="#">73415</a>
Overview	<a href="#">MMCX RF Connectors</a>
Product Name	MMCX
Style	Cable
Type	Microminiature
UPC	884982653443
Wire/Cable Type	RG-174, RG-188, RG-316

**Physical**

Gender	Plug
Keying to Mating Part	None
Net Weight	0.830/g
Orientation	Straight
PCB Mounting	N/A
Packaging Type	Bag
Panel Mount	No
Panel Mount Method	N/A
Reverse Polar	No

**Electrical**

Frequency	6 GHz
Impedance	50Ω
Power / Voltage	VOLTAGE: 170 Vrms@Sea Level

**Material Info**

**Reference - Drawing Numbers**

Application Specification	735970550-000
Sales Drawing	SD-73415-125-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant with Exemption 6(c)**

**REACH SVHC**

Contained Per - D(2020)9139-DC (19 Jan 2021)

lead

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

50 Image

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[73415 Series](#)

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**