

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0791077059

Status:

Active

Overview:

Milli-Grid Connector System

Description:

2.00mm Pitch Milli-Grid Receptacle, Vertical, Through Hole, Dual Row, 3.00mm Tail Length, 0.76µm Gold (Au) Selective Plating, 20 Circuits, Lead-Free



Documents:

3D Model

3D Model (PDF)

Drawing (PDF)

Product Specification PS-79107-001 (PDF)

Application Specification 503940001-AS-000 (PDF)

Packaging Specification PK-70873-0180-001 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	PCB Receptacles
Series	79107
Application	Board-to-Board, Signal
Overview	Milli-Grid Connector System
Product Name	Milli-Grid
UPC	822348474783
Physical	
Circuits (Loaded)	20
Circuits (maximum)	20
Color - Resin	Black
Durability (mating cycles max)	50
Glow-Wire Capable	No
Lock to Mating Part	None
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Tin
Material - Resin	High Temperature Thermoplastic
Net Weight	0.586/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	3.00mm
PCB Locator	No
PCB Retention	None
PCB Thickness - Recommended	1.60mm
Packaging Type	Tube
Pitch - Mating Interface	2.00mm
Pitch - Termination Interface	2.00mm
Plating min - Mating	0.762µm
Plating min - Termination	1.905µm
Polarized to Mating Part	No
Polarized to PCB	No
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-55° to +105°C
Termination Interface: Style	Through Hole
Electrical	
Current - Maximum per Contact	1.0A
Voltage - Maximum	125V
Solder Process Data	
Duration at Max. Process Temperature (seconds)	010
Lead-freeProcess Capability	WAVE
Max. Cycles at Max. Process Temperature	001

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - D(2020)9139-DC (19 Jan 2021)	
Halogen-Free	
Status	
Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series

79107 Series

Mates With

Milli-Grid Header [87758](#) , [87759](#) , [87760](#) , [87831](#) , [87832](#)
 Milli-Grid Low-Halogen Header [151117](#) , [151118](#) , [151119](#) , [151120](#)

Process Temperature max. C

260

Material Info

Reference - Drawing Numbers

Application Specification

503940001-AS-000

Packaging Specification

PK-70873-0180-001

Product Specification

PS-79107-001

Sales Drawing

SDA-79107-++++-001, SDA-79107-XXXX

This document was generated on 07/29/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION