

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0797580002](#)  
**Status:** **Active**  
**Overview:** Off-the-Shelf Pre-Crimped Leads  
**Description:** Pre-Crimped Lead Micro-Fit 3.0 Female-to-Micro-Fit 3.0 Female, Tin (Sn) Plating, 150.00mm Length, 20 AWG, Black

**Documents:**

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Cable Assemblies
Series	<a href="#">79758</a>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Micro-Fit 3.0 Crimp Terminals
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	Micro-Fit 3.0
UPC	884982052659

**Physical**

Cable Length	150.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	1.045/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	20
Wire/Cable Type	UL 1061

**Material Info**

**Reference - Drawing Numbers**

Sales Drawing	SD-797580001-001
---------------	------------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
Jan 2021)

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[79758](#) Series

**Use With**

Micro-Fit 3.0 Receptacle Housings [43025](#)  
, [43645](#) <br>Micro-Fit TPA Receptacle  
Housings [171850](#) , [172952](#) <br>Micro-Fit  
BMI Panel Mount Receptacle Housings<br>  
[44133](#) , [46623](#)