

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: **0797580016**
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead Pico-SPOX Female-to-Pico-SPOX Female, Tin (Sn) Plating, 300.00mm Length, 24 AWG, Black

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)
[Datasheet \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	<u>79758</u>
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Pico-SPOX Crimp Terminals
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	Pico-SPOX
UPC	884982052802

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	Black
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.944/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	24
Wire/Cable Type	UL 1061

Material Info

Reference - Drawing Numbers
Sales Drawing SD-797580001



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per
-ED/01/2018 (15
January 2018)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

79758 Series

Use With

Pico-SPOX Housings 87439