

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0797581010](#)
Status: **Active**
Overview: Off-the-Shelf Pre-Crimped Leads
Description: Pre-Crimped Lead Pico-EZmate Female-to-Pico-EZmate Female, Gold (Au) Plating, 300.00mm Length, 28 AWG, White

Documents:

[Drawing \(PDF\)](#)

[Datasheet \(PDF\)](#)

[RoHS Certificate of Compliance \(PDF\)](#)

General

Product Family	Cable Assemblies
Series	79758
Assembly Configuration	Pre-crimped Lead Only
Connector to Connector	Pico-EZmate Crimp Terminals
Overview	<u>Off-the-Shelf Pre-Crimped Leads</u>
Product Name	Pico-EZmate
UPC	889056818605

Physical

Cable Length	300.00mm
Circuits (Loaded)	1
Color - Resin	White
Gender	Female-Female
Material - Metal	Phosphor Bronze
Material - Plating Mating	Gold
Material - Plating Termination	Gold
Net Weight	0.450/g
Packaging Type	Bag
Single Ended	No
Termination Interface: Style	Crimp or Compression
Wire Size AWG	28
Wire/Cable Type	UL 1516

Material Info

Reference - Drawing Numbers

Sales Drawing	2012341212-000
---------------	----------------



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
D(2020)9139-DC (19
Jan 2021)

Halogen-Free

Status

Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[79758 Series](#)

Use With

Crimp Receptacle Housings [78172](#)