

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0847000002](#)
Status: **Active**
Overview: [Brad Industrial Ethernet Solutions](#)
Description: Field-Attachable Plug Kit, RJ-45

Documents:
[3D Model](#) [3D Model \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

General
Product Family Field Attachable / Accessories
Series [84700](#)
IP Rating IP67
Material - Contact Phosphor Bronze
Overview [Brad Industrial Ethernet Solutions](#)
Product Name RJ45
Type Field Attachable Connector
UPC 756054460412


Physical
Cable Diameter 1.60mm (.063")
Coupling Type Overmolded Cable
Diagnostics / LEDs No
Diagnostics Port No
Gender N/A
Keyway N/A
Material - Connector Body Polypropylene
Material - Coupling Nut Die-Cast Zinc
Material - Plating Mating Gold
Net Weight 26.761/g
Orientation N/A
Poles 4
Temperature Range - Operating -40°C to +85°C
Wire Size AWG 22 to 28

Electrical
Current - Maximum per Contact 1.5A
Voltage - Maximum 150V AC

Solder Process Data
Lead-freeProcess Capability N/A

Material Info

Reference - Drawing Numbers
Sales Drawing SD-84700-012



Series image - Reference only

EU ELV
Not Relevant

EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per	
-ED/01/2018 (15	
January 2018)	
Halogen-Free	
Status	
Not Low-Halogen	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
[84700 Series](#)

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION