



MATERIALS AND FINISHES

MCX PLUG (50 OHM): SEE SD-73366-001

SHRINK TUBE: VERSAFIT

CABLE: RG316



CABLES WILL BE INDIVIDUALLY BAGGED

BAG LABEL:
MOLEX: P/N
DATE CODE

89761-6136	5.43±.25	138.00±6.35
89761-6135	18.00±.35	457.20±8.89
89761-6134	12.00±.25	304.80±6.35
89761-6133	6.00±.25	152.40±6.35
89761-6132	19.50+-.2/-0	495.3+5.08/-0
89761-6131	16.25+-.2/-0	412.8+5.08/-0
89761-6130	1.350±.100	34.29±2.54
PART NO.	IN	MM
DIM A		

PS-89675-362	PRODUCT SPECIFICATION
SPECIFICATION	DESCRIPTION

CHG: ADDED -6136 EC NO: URF2015-0160 DRWN:JLEE02 2014/10/07 CHKD:SSS 2014/10/07 APPR:MSPINK 2014/10/07 REV A4	QUALITY SYMBOLS = 0 = 0	GENERAL TOLERANCES (UNLESS SPECIFIED) <table border="1"> <thead> <tr> <th></th> <th>mm</th> <th>INCH</th> </tr> </thead> <tbody> <tr> <td>4 PLACES</td> <td>± .---</td> <td>± .---</td> </tr> <tr> <td>3 PLACES</td> <td>± .---</td> <td>± .---</td> </tr> <tr> <td>2 PLACES</td> <td>± .---</td> <td>± .---</td> </tr> <tr> <td>1 PLACE</td> <td>± .---</td> <td>± .---</td> </tr> </tbody> </table>		mm	INCH	4 PLACES	± .---	± .---	3 PLACES	± .---	± .---	2 PLACES	± .---	± .---	1 PLACE	± .---	± .---	DIMENSION STYLE MM/IN DRAWN BY: JDW DATE: 2008/07/24 CHECKED BY: JYL DATE: 2008/07/24 APPROVED BY: JDW DATE: 2008/07/24	SCALE TITLE: CA, MCX PLUG RA 50 OHMS, RG316 EWR-3704, CA-MCX MOLEX INCORPORATED DOCUMENT NO. SD-89761-613 SHEET NO. 1 OF 1
		mm	INCH																
	4 PLACES	± .---	± .---																
	3 PLACES	± .---	± .---																
2 PLACES	± .---	± .---																	
1 PLACE	± .---	± .---																	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE TABLE SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																