

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0901420030](#)  
**Status:** **Active**  
**Overview:** [C-Grid III Interconnects](#)  
**Description:** 2.54mm Pitch C-Grid III Crimp Housing Dual Row, 30 Circuits, Black

**Documents:**

[Drawing \(PDF\)](#) [Packaging Specification PK-90142-0001-001 \(PDF\)](#)  
[Product Specification PS-99020-0001-001 \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**Agency Certification**

CSA LR19980  
 UL E29179

**General**

Product Family Crimp Housings  
 Series [90142](#)  
 Application Signal, Wire-to-Board  
 Overview [C-Grid III Interconnects](#)  
 Product Name C-Grid III  
 UPC 800753657298


**Physical**

Breakaway No  
 Circuits (maximum) 30  
 Color - Resin Black  
 Flammability 94V-1  
 Gender Receptacle  
 Glow-Wire Capable No  
 Keying to Mating Part None  
 Lock to Mating Part Yes  
 Material - Resin PPO  
 Net Weight 2.000/g  
 Number of Rows 2  
 Packaging Type Bag  
 Panel Mount No  
 Pitch - Mating Interface 2.54mm  
 Pitch - Termination Interface 2.54mm  
 Polarized to Mating Part Yes  
 Ports 0  
 Stackable No  
 Temperature Range - Operating -55° to +105°C

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-90142-0001-001  
 Product Specification PS-99020-0001-001  
 Sales Drawing SD-90142-001



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
 D(2020)9139-DC (19  
 Jan 2021)

**Halogen-Free**

**Status**

**Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[90142](#) Series

**Mates With**

C-Grid III Header, Dual Row [90122](#) , [90130](#) ,  
[90131](#)

**Use With**

C-Grid III Crimp Terminal [90119](#) <br> C-  
 Grid III Pre-Crimped Lead [797582022](#) ,  
[797582023](#)