

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0903270312](#)
Status: **Active**
Overview: [Picoflex Ribbon-Cable Connectors](#)
Description: Picoflex PF-50, Low Profile, IDT Receptacle, 12 Circuits, White, Tin (Sn) Plated, Bag

Documents:

[3D Model](#) [Product Specification PS-99020-0011-001 \(PDF\)](#)
[3D Model \(PDF\)](#) [Packaging Specification PK-90327-001-001 \(PDF\)](#)
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA LR19980
 UL E29179

General


Product Family Ribbon Cable / Wire Trap Connectors
 Series [90327](#)
 Comments Low Profile
 Component Type Housing
 Glow-Wire Capable No
 Overview [Picoflex Ribbon-Cable Connectors](#)
 Product Name Picoflex
 UPC 800753538146

Physical

Circuits (Loaded) 12
 Circuits (maximum) 12
 Color - Resin White
 Durability (mating cycles max) 30
 Entry Angle Vertical
 Flammability 94V-0
 Lock to Mating Part Yes
 Material - Metal Phosphor Bronze
 Material - Plating Mating Tin
 Material - Plating Termination Tin
 Material - Resin Polyester
 Net Weight 0.737/g
 Number of Rows 2
 PCB Locator No
 PCB Retention None
 Packaging Type Bag
 Pitch - Mating Interface 1.27mm
 Pitch - Termination Interface 1.27mm
 Polarized to Mating Part Yes
 Polarized to PCB No
 Shrouded Fully
 Stackable No
 Surface Mount Compatible (SMC) N/A
 Temperature Range - Operating -40° to +105°C
 Termination Interface: Style IDT or Pierce
 Wire Insulation Diameter 1.00mm max.
 Wire Size AWG 26, 28
 Wire/Cable Type Ribbon Cable

Electrical

Current - Maximum per Contact 1.2A
 Voltage - Maximum 250V



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Low-Halogen

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[90327](#) Series

Mates With

Low Profile Vertical [90325](#) , Low Profile
 Right Angle [90800](#) , [90715](#) , [90814](#) , [90779](#)
 Vertical, [91714](#) 1.27mm Pitch Picoflex PF-50
 Header

Application Tooling | FAQ

Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global

Description	Product #
Extractor Tool for Connectors	621006000
Extraction Tool for Picoflex PF-50 Connectors, 4-26 Circuits	690081070
PremiumGrade Hand Crimp Tool	690081090

Material Info**Reference - Drawing Numbers**

Packaging Specification
Product Specification
Sales Drawing

PK-90327-001-001
PS-99020-0011-001
SDA-90327-001

for Picoflex PF-50
IDT Receptacle,
4-26 Circuits, 26
or 28 AWG Flat
Cable, 1.00mm max.
thickness

Arbor Press Fixture [690201902](#)

Arbor Press Fixture [690201908](#)

Semi-Automatic [691271001](#)

Bench Press PB14

for 4-26 Circuit

Semi-Automatic [691271004](#)

PB14 Bench Press

with Auto De-reeling

Assembly of De- [691275045](#)

Tape Unit for

PB14 Part Number

691271001

This document was generated on 08/17/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION