

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010329](#)
Status: **Active**
Overview: [GWconnect Heavy Duty Connectors \(HDC\)](#)
Description: GWconnect Crimp Contact Insert, Male, 46-Pole, 16A, Numbered 1-46, for Crimp Contacts, Size 24B «104x27»

Documents:
[RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification	
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Component Size	24B «104X27»
Component Type	Inserts - Crimp Contact
Insert Series	S-EE
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	CSA C22.2 NO. 182.3, EN 60664-1, EN 61984, UL 1977
UPC	887191883779
Physical	
Durability (mating cycles max)	500
Flammability	UL 94V-0
Gender	Male
Insert Color	Grey
Material - Insert	Polycarbonate
Net Weight	76.000/g
Number of Rows	4
Packaging Type	Bag
Polarized to Mating Part	Yes
Poles	46
Temperature Range - Operating	-40° to +125°C
Electrical	
Current - Maximum per Contact	16.0A
Voltage - Maximum	500V
Material Info	
Engineering Number	7346.6194.0



Series image - Reference only

EU ELV Not Relevant	
EU RoHS Compliant with Exemption 6(c) REACH SVHC Not Reviewed Halogen-Free Status Not Reviewed For more information, please visit Contact US	China RoHS 50 Image Not Relevant Not Contained

Search Parts in this Series
[93601](#) Series

Mates With
[936010327](#) Female Crimp Contact Insert

Use With
Turned Contacts - Male

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION