

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0936010675

Status:

Active

Overview:


GWconnect Heavy Duty Connectors (HDC)

Description:

GWconnect STD - Standard, Single Lever Bulkhead Mount Housing, Polyamide, with 1 Lever, Right Angle, with Gasket, Size 3A«21x21», M20 Thread, Black

Documents:	
Drawing (PDF)	RoHS Certificate of Compliance (PDF)

Agency Certification	
CSA	256883
UL	E249674
General	
Product Family	Industrial Connectors / Enclosures
Series	93601
Comments	IP67 with screw gasket.
Component Size	3A «21x21»
Component Type	Single Lever Bulkhead Housing
IP Rating	IP66, IP67
Overview	GWconnect Heavy Duty Connectors (HDC)
Product Category	Heavy Duty Connectors
Product Name	GWconnect
Standard	ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
Type	STD
UPC	887191842028
Physical	
Flammability	UL 94V-0
Housing Color	Black RAL 9005
Lock to Mating Part	Yes
Material - Gasket	NBR
Material - Housing	Polyamide
Material - Lever	Polyamide
Mounting Style	Bulkhead
Net Weight	17.000/g
Number of Levers	1
Packaging Type	Bag
Thread Size	M20
Thread Type	(M) Metric
Electrical	
Voltage - Maximum	230V / 400V
Material Info	
Engineering Number	7803.6225.1
Reference - Drawing Numbers	
Sales Drawing	936010675-000



Series image - Reference only

EU ELV	
Not Relevant	
EU RoHS	China RoHS
Compliant	
REACH SVHC	
Not Contained Per - ED/71/2019 (16 July 2019)	
Halogen-Free	
Status	
Not Reviewed	
For more information, please visit Contact US	
China ROHS	Green Image
ELV	Not Relevant
RoHS Phthalates	Not Contained

Search Parts in this Series
93601 Series
Use With
Size 3A «21x21» S-A, S-D, and S-Q Inserts

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION