

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936010680](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Single Lever Hood, Polyamide, with 2 Pegs, Top Entry, Size 3A «21x21», M20 Thread, Grey White

Documents:

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

Agency Certification

CSA 256883
 UL E249674

General

Product Family Industrial Connectors / Enclosures
 Series [93601](#)
 Comments IP67 with screw gasket.
 Component Size 3A «21x21»
 Component Type Single Lever Hood
 IP Rating IP66
 Overview [GWconnect Heavy Duty Connectors \(HDC\)](#)
 Product Category Heavy Duty Connectors
 Product Name GWconnect
 Standard ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984
 Type STD
 UPC 887191842073

Physical

Entry Location Top
 Flammability UL 94V-0
 Hood Color Grey White RAL 9002
 Lock to Mating Part Yes
 Material - Hood Polyamide
 Material - Peg Polyamide
 Net Weight 12.200/g
 Number of Pegs 2
 Packaging Type Bag
 Thread Size M20
 Thread Type (M) Metric

Electrical

Voltage - Maximum 230V / 400V

Material Info

Engineering Number 7803.6227.0

Reference - Drawing Numbers

Sales Drawing 936010680-000



EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per -
 D(2020)9139-DC (19
 Jan 2021)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601 Series](#)

Use With

Size 3A «21x21» S-A, S-D, and S-Q Inserts