

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [0936011167](#)
Status: **Active**
Overview: GWconnect Heavy Duty Connectors (HDC)
Description: GWconnect STD - Standard, Single Lever Hood, Die-cast Aluminum, with 2 Pegs, Top Entry, Size 10A «49x16», Extended M20 Thread, Grey

Documents:

| | |
|--------------------------------|--|
| 3D Model | Drawing (PDF) |
| 3D Model (PDF) | RoHS Certificate of Compliance (PDF) |

Agency Certification

| | |
|-----|---------|
| CSA | 256883 |
| UL | E249674 |

General

| | |
|------------------|---|
| Product Family | Industrial Connectors / Enclosures |
| Series | 93601 |
| Component Size | 10A «49X16» |
| Component Type | Single Lever Hood |
| IP Rating | IP66 |
| Overview | GWconnect Heavy Duty Connectors (HDC) |
| Product Category | Heavy Duty Connectors |
| Product Name | GWconnect |
| Standard | ANSI/UL 50, ANSI/UL 50 E, CSA C22.2 No.94-1-2, EN 61984 |
| Type | STD |
| UPC | 887191875248 |

Physical

| | |
|---------------------|-------------------|
| Entry Location | Top |
| Hood Coating | Polyester Powder |
| Hood Color | GREY RAL 7037 |
| Lock to Mating Part | Yes |
| Material - Hood | Die-cast Aluminum |
| Material - Peg | Stainless Steel |
| Net Weight | 135.740/g |
| Number of Pegs | 2 |
| Packaging Type | Bag |
| Thread Size | M20 |
| Thread Type | (M) Metric |

Electrical

| | |
|-------------------|------|
| Voltage - Maximum | 500V |
|-------------------|------|

Material Info

| | |
|--------------------|-------------|
| Engineering Number | 7810.4550.0 |
|--------------------|-------------|

Reference - Drawing Numbers

| | |
|---------------|---------------|
| Sales Drawing | 936011167-000 |
|---------------|---------------|



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

REACH SVHC

Not Contained Per - ED/71/2019 (16 July 2019)

Halogen-Free

Status

Not Reviewed

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

China RoHS

Green Image

Not Relevant

Not Contained

Search Parts in this Series

[93601 Series](#)

Use With

Size 10A «49x16» S-A and S-D Inserts