

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:


0945180201

Status:

Active

Description:

High Normal Force Tabs, Tin Plated Brass, AWG 14-18



Series image - Reference only

Documents:

Drawing (PDF)

Packaging Specification 945180001-PK-000 (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Crimp Terminals
Series	94518
Application	Power, Wire-to-Board
Crimp Quality Equipment	Yes
Product Name	High Normal Force (HNF) Termin
UPC	800754333450

Physical	
Gender	Female
Material - Metal	Brass
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Net Weight	0.720/g
Packaging Type	Reel
Plating min - Mating	2.540µm
Plating min - Termination	2.540µm
Wire Insulation Diameter	2.80-3.80mm
Wire Size AWG	14, 16, 18
Wire Size mm²	1.00-2.50

Material Info

Reference - Drawing Numbers	
Packaging Specification	945180001-PK-000
Sales Drawing	945180001-000

EU ELV
Compliant

EU RoHS Compliant REACH SVHC Not Contained Per - D(2020)9139-DC (19 Jan 2021) Halogen-Free Status Low-Halogen	China RoHS
---	-------------------

For more information, please visit [Contact US](#)

China ROHS	Not Relevant
ELV	Compliant
RoHS Phthalates	Not Contained

Search Parts in this Series
94518 Series

Application Tooling | FAQ
Tooling specifications and manuals are found by selecting the products below. Crimp Height Specifications are then contained in the Application Tooling Specification document.

Global	
Description	Product #
Extraction and Activation Tool	638132700
Hand Crimp Tool for HNF Female Terminals	638235700
Hand Crimp Tool for HNF Female Terminals	638250600
FineAdjust Applicator for High Normal Force Female Crimp Terminals	639023600

This document was generated on 08/09/2021

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION