

Heat Shrink Tube Assortments 3:1 (200 pcs) Type: 2107CA135

This range of shrinking tubes is particularly suitable for hobbyists, craftsmen, field service, service workshops, electronics and the laboratory needs. 2 x 100 pieces of shrinking ration 3:1 standard shrinking tube for a range of application diameter from 1.5 to 18 mm. Thin wall tubing with hot melt adhesive in the Black hose. The heat-shrink tubing can be used for insulation, protective covering of components, as anti-kink protection, protection against corrosion, as well as repair of cables and lines, and much more be used. High quality product from industrial applications.



Technical Specifications

Material: PE, shrink temperature (min.): 90 °C, shrink temperature (max.): 125 °C, operating temperature: -40 °C to +125 °C, tensile strength (min.): 10.4 MPa, dielectric strength 15 kV (30 sec.), industrial quality. All hoses comply with RoHS directives and are halogen-free. Further technical data on the components included, are printed on the inside of the covers.

Content

Two transparent assortment boxes, min. 100 heat shrink tubing sections per each assortment.

50 pieces - Ø 1,6 mm - length 32 mm, 40 pieces - Ø 2,4 mm - length 32 mm, 40 pieces - Ø 3,2 mm - length 32 mm, - 30 pieces - Ø 4.8 mm - length 65 mm, 16 pieces - Ø 6,4 mm - length 65 mm, 10 pieces - Ø 7,9 mm - length 65 mm, 8 pieces - Ø 9.5 mm length - 95 mm, 6 pieces - Ø 12,7 mm length - 95 mm.