

VOLTCRAFT® - TOP PERFORMANCE IN EVERY WAY

For more than 40 years, our product range has been dynamically adapting to the constant changes in the industry. We commit to offering first-class quality to our customers while delivering an excellent cost-performance ratio. This philosophy remains the cornerstone of Voltcraft's success.

DT-70 THERMOMETER



Item no: 2464281

The product is a temperature measuring device with 3 m sensor cable. It is suitable for uses such as aquariums, terrariums, and plant breeding. The product is food safe.

FEATURES

High/Low temperature alarm // Hold function // °C / °F switchable // Food safe

TECHNICAL DATA

Power supply	1x CR2032 3 V Li-ion button cell battery
Battery life	approx. 12 months
Temperature measuring range	-40 to +70 °C
Sensor type	NTC
Resolution	0.1 °C
Accuracy	±0.5 °C @ -20 to +25 °C ±1 °C @ -40 to -20 °C ±1 °C @ +25 to +70 °C
Measuring rate	6s
Sensor probe length	approx. 3 m
Display dimensions (W x H)	53 x 26 mm
Ingress protection	IP65
Food safe (HACCP)	Yes
Operating/storage conditions	-10 to +50 °C, 10 - 90% RH
Dimensions (L x W x H)	66.6 x 14.3 x 66.6 mm (without holder) 66.6 x 33.5 x 71 mm (with holder)
Weight	76.5 g (holder and battery)



CONTENTS

Product // Detachable stand // Temperature probe (3 meters) // 1x CR2032 3 V battery //
Operating instructions

This is a publication by Conrad Electronic SE, Klaus-Conrad-Str. 1, D-92240 Hirschau (www.conrad.com).

All rights including translation reserved. Reproduction by any method (e.g. photocopying, microfilming or the capture in electronic data processing systems) requires prior written approval from the editor. Reprinting, also in part, is prohibited. This publication reflects the technical status at the time of printing.

Copyright by Conrad Electronic SE. 2464281_V1_0622_en_ds 9007199834463627 I2/O1 en